



Inch table

Dimensions in: inches - millimeters

¹ d ₃	² d ₁ Thread	³ l ₁	d ₂	k	l ₂
0.75 19.1	10 x 24	1.00 25.4	0.13 3.3	0.25 6.4	0.75 19.1
0.75 19.1	10 x 24	1.50 38.1	0.13 3.3	0.25 6.4	1.25 31.8
0.75 19.1	10 x 24	2.00 50.8	0.13 3.3	0.25 6.4	1.75 44.5
1.00 25.4	1/4 x 20	1.50 38.1	0.16 4.1	0.31 7.9	1.25 31.8
1.00 25.4	1/4 x 20	2.00 50.8	0.16 4.1	0.31 7.9	1.75 44.5
1.00 25.4	1/4 x 20	2.50 63.5	0.16 4.1	0.31 7.9	2.25 57.2
1.13 28.7	5/16 x 18	1.50 38.1	0.20 5.1	0.38 9.7	1.25 31.8
1.13 28.7	5/16 x 18	2.00 50.8	0.20 5.1	0.38 9.7	1.75 44.5
1.13 28.7	5/16 x 18	2.50 63.5	0.20 5.1	0.38 9.7	2.25 57.2
1.25 31.8	3/8 x 16	2.00 50.8	0.25 6.4	0.44 11.2	1.75 44.5
1.25 31.8	3/8 x 16	3.00 76.2	0.25 6.4	0.44 11.2	2.75 69.9
1.25 31.8	1/2 x 13	3.00 76.2	0.34 8.6	0.50 12.7	2.75 69.9

Specification

- Low carbon steel
 - Heat treated
 - Blackened finish
- RoHS compliant

Information

DPHS knurled thumb screws are applied where permanent location of one part in relation to another is desired. The dog point is usually positioned in a hole or a slot.

see also...

- *Knurled Thumb Screws KHS (Steel or Stainless Steel)* → page 708

<p>How to order</p> <p>¹ ² ³</p> <p>DPHS-0.75-10X24-1.00</p>	1	Handle diameter d ₃
	2	Thread d ₁
	3	Length l ₁

1.1
1.2
1.3
1.4
2.1
2.2
2.3
2.4