



3 Type

- A Without locking element
- N With locking element

Inch table

| 1 | | 2 | | | Dimensions in: inches - millimeters | | |
|----------------|--------------------------|----------------|----------------|----------------|-------------------------------------|--------------|-------------|
| d ₁ | d ₂ Thread | d ₃ | h ₁ | h ₂ | | | |
| 2.25 57.2 | 1/4 x 20 | 5/16 x 18 | 3/8 x 16 | 3/8 x 24* | 0.84 21.3 | 0.78 19.8 | 0.28 7.1 |

*This size is only available in Type A

Specification

- Five-lobed knob
Polypropylene plastic
 - Temperature resistant up to 275 °F (135 °C)
 - Black, matte finish
- Tapped insert / hexagon nut
Steel, zinc plated
- RoHS compliant

Information

FSK five-lobed knobs are perfect for light duty clamping on office chairs for example, but can be used for a variety of other applications.

On request

- Additional thread sizes

| | |
|---|----------------------------------|
| How to order 1 2 3 FSK-2.25-1/4X20-A | 1 Handle diameter d ₁ |
| | 2 Thread d ₂ |
| | 3 Type |