



SS Stainless Steel

Metric table

Dimensions in: millimeters - inches

1 d_1	2 d_2 Thread	3 Length l		d_3	h_1	h_2	t min.
30 1.18	M 6	20 0.79	30 1.18	14 0.55	24 0.94	15 0.59	9 0.35
40 1.57	M 8	20 0.79	30 1.18	16 0.63	28 1.10	18 0.71	13 0.51
50 1.97	M 10	25 0.98	30 1.18	18 0.71	32 1.26	20 0.79	16 0.63

Specification

- Six-lobed knob
Nylon plastic
 - Temperature resistant up to 230 °F (110 °C)
 - Glass filled
 - Black, matte finish
- **LBX**
Tapped insert
Stainless steel AISI 304
- **LPX**
Threaded stud
Stainless steel AISI 304
- *Plastic Characteristics* → page 2135
- *Stainless Steel Characteristics* → page 2143
- **RoHS compliant**

Information

LBX is an economical but durable six-lobed knob for many applications.

How to order (Tapped insert) LBX-50-M10	1 Handle diameter d_1
	2 Thread d_2
How to order (Threaded stud) LPX-40-M8-30	1 Handle diameter d_1
	2 Thread d_2
	3 Length l

1.1
1.2
1.3
1.4
2.1
2.2
2.3
2.4

