



**Inch table**

1		2						
d <sub>1</sub>	d <sub>2</sub> Thread		d <sub>3</sub>	d <sub>4</sub>	l <sub>1</sub>	l <sub>2</sub>	l <sub>3</sub>	l <sub>4</sub>
1.97 50	5/16 x 18	3/8 x 16	.79 20	.98 25	.98 25	.51 13	.39 10	.87 22
2.36 60	3/8 x 16	1/2 x 13	.98 25	1.18 30	1.14 29	.55 14	.43 11	.98 25
2.76 70	1/2 x 13	5/8 x 11	1.18 30	1.42 36	1.26 32	.63 16	.47 12	1.06 27

Dimensions in: inches - millimeters

**Specification**

- Nylon plastic
  - Black, glass fiber reinforced
  - Temperature resistant up to 230 °F (110 °C)
- Hub bushing
  - Steel, zinc plated, molded-in
- RoHS compliant

**Information**

LMAQ quick release six lobed knobs are distinguished by their modern design. An excellent choice where medium-heavy duty clamping is required. Good shock-resistant properties.

Quick release knobs are used in such applications where the knob has to be completely removed after the releasing operation and then placed again very rapidly for re-clamping.

The knob is tilted over the threaded spindle. When in position, the knob is brought into a straight position for meshing of the two threads on knob and spindle. The knob will then have to be turned only by a fraction of a rotation to achieve clamping.

**On request**

- Metric sizes

How to order 1 2 <b>LMAQ-50-5/16X18</b>	1 Handle diameter d <sub>1</sub>
	2 Thread d <sub>2</sub>