




Inch



Inch table

1				2					Dimensions in: inches / millimeters					
l ₁		s			l ₂		d ₂		h		l ₃		d ₁	
		Square											Ø Handle	
7.00		V 3/8	V 1/2	V 5/8	7.81		1.56		0.59		2.94		1.00	
177.8					198.4		39.6		15		74.7		25.4	
10.00		V 1/2	V 5/8	V 3/4	11.00		2.06		0.88		2.94		1.00	
254					279.4		52.3		22.4		74.7		25.4	
12.00		V 1/2	V 3/4	-	13.50		2.50		0.88		3.34		1.09	
304.8					342.9		63.5		22.4		84.8		27.7	

Specification

Crank body

- Steel
- Stamping
- Riveted
- Slim profile gears
- Reversing lever control in wrench head

Revolving Handles DIN 98

Steel, zinc plated, blue passivated finish

RoHS

On request

- Other sizes, bore or hex openings
- Fixed or revolving handles
- With handles in steel or plastic

The combination of crank and ratchet arm of these ratcheting crank handles LR 318 makes machinery adjustment faster, easier and safer.

Through hole design allows bolts or shafts to pass entirely through the ratcheting socket so, where required, nuts can then be secured at any part of the threaded length of the bolt or threaded shaft.

Technical Information

Keyways WN 6885 / DIN 6885-1

Page

QVX

How to order		1	Length l ₁
LR 318-7.00-V3/8		2	Square s