



Universal table

Dimensions in: millimeters - inches

¹ b	² d ₁	³ l ₁	d ₂	h ₁	h ₂	h ₃	l ₂	t
21 .83	B 6.5	93.5 3.68	10.5 .41	36 1.42	30 1.18	6 .24	112 4.41	7 .28
24.5 .96	B 6.5	117 4.61	10.5 .41	41 1.61	34 1.34	6 .24	139 5.47	9 .35
24.5 .96	B 8.5	117 4.61	13 .51	41 1.61	34 1.34	6 .24	139 5.47	9 .35
27 1.06	B 6.5	132 5.20	10.5 .41	45 1.77	37 1.46	9 .35	156 6.14	7 .28
27 1.06	B 8.5	132 5.20	13 .51	45 1.77	37 1.46	7 .28	156 6.14	9 .35
28 1.10	B 8.5	179 7.05	13 .51	50 1.97	42 1.65	8 .31	204 8.03	9 .35

Specification

- **MF**
Nylon plastic
- Black, RAL 9005, matte finish ● **SW**
- Glass fiber reinforced
- Temperature resistant up to 230 °F (110 °C)
- **MFE**
Polypropylene plastic
- Black, RAL 9005, matte finish ● **SW**
- Glass fiber reinforced
- Temperature resistant up to 212 °F (100 °C)
- Mounting holes
Counterbored for inch or metric socket cap screws
- RoHS compliant

On request

- Additional colors
- Various metric and inch size fasteners and kit packaging

Information

The shape of MF and MFE cabinet "U" handles has good ergonomic features. Because of the style and durability of these handles, they are suitable for most industries.

The MFE series is the economical version of the MF series.

see also...

- Cabinet "U" Handles GN 565.1

How to order (Nylon plastic) ¹ ² ³ ⁴ MF-27-B6.5-132-SW	1 Handle width b
	2 Bore d ₁
	3 Length l ₁
	4 Color

How to order (Polypropylene plastic) ¹ ² ³ ⁴ MFE-28-B8.5-179-SW	1 Handle width b
	2 Bore d ₁
	3 Length l ₁
	4 Color

1.1
1.2
1.3
1.4
2.1
2.2
2.3
2.4