



**Metric table**

Dimensions in: millimeters - inches

<sup>1</sup> b	<sup>2</sup> d	<sup>3</sup> l <sub>1</sub>	h <sub>1</sub>	h <sub>2</sub>	l <sub>2</sub>	l <sub>3</sub>
25 0.98	B 6.5	110 4.33	44 1.73	24 0.94	130 5.12	88 3.46

**Specification**

- Nylon plastic
  - Black, RAL 9005, matte finish
  - Glass fiber reinforced
  - Temperature resistant up to 230 °F (110 °C)
- Cover strip
  - Orange, RAL 2004, matte finish
- Mounting holes
  - Through holes for inch or metric hex cap screws or low socket cap screws
- *Plastic Characteristics* → page 2135
- [RoHS compliant](#)

**On request**

- Additional colors
- Various metric and inch size fasteners and kit packaging

**Information**

The MFA pull handle is a “safety handle” with a 15° angle, and is used where a reach-through of the fingers is not permitted.

How to order	<sup>1</sup> Handle width b
<sup>2</sup> MFA-25-B6.5-110	<sup>2</sup> Bore d
<sup>3</sup>	<sup>3</sup> Length l <sub>1</sub>

1.1  
1.2  
1.3  
1.4  
2.1  
2.2  
2.3  
2.4