



**Metric table**

<sup>1</sup> $d_1$	<sup>2</sup> $d_2$ Bore diameter	$d_3$	$l_1$	$l_2$
20 0.79	B 8	14 0.55	37 1.46	34 1.34

Dimensions in: millimeters - inches

**Specification**

- Plastic  
PVC
- Temperature resistant up to 158 °F (70 °C)
- Black
- Molded blind bore
- Push-fit mounting
- *Plastic Characteristics* → page QVX
- **RoHS compliant**

**Information**

The MVP-CON tapered handle offers a comfortable and elastic grip.  
 see also...  
 • *Cylindrical Handles MVP* → page QVX

How to order <sup>1</sup> <sup>2</sup> <b>MVP-CON-20-B8</b>	1 Handle diameter $d_1$
	2 Bore diameter $d_2$

1.1  
1.2  
1.3  
1.4  
2.1  
2.2  
2.3  
2.4

