



Metric table

Dimensions in: millimeters - inches

d ₁		d ₂	l ₁	l ₂	s
Pipe thread	Fine thread				
G 1/4	-	20 0.79	6 0.24	3 0.12	17 0.67
G 3/8	-	22 0.87	7 0.28	3 0.12	19 0.75
-	M 20 x 1.5	26 1.02	8 0.31	3.5 0.14	21 0.83
G 1/2	-	28 1.10	8 0.31	3.5 0.14	24 0.94
G 3/4	-	33 1.30	11 0.43	3.6 0.14	28 1.10
G 1	-	42 1.65	13 0.51	4.7 0.19	36 1.42
G 1 1/4	-	54 2.13	12 0.47	4.2 0.17	46 1.81

Specification

- Body
Plastic
Nylon (Polyamide)
- Transparent
- Temperature resistant up to 194 °F (90 °C)
- Seal
Rubber NBR (Perbunan®)
- RoHS compliant

Information

TLT fluid sight glasses are a low cost choice for light duty applications.

The seal comes unassembled.

see also...

- Fluid Sight Glasses EN 541 (Inch / Metric, with or without Reflector)

<p>How to order</p> <p>TLT-G3/8</p>	<p>1 Pipe thread d₁ (Fine thread d₁)</p>
--	--