



Metric table

Dimensions in: millimeters - inches

d ₁	d ₂ Thread	d ₃	d ₄	h ₁	h ₂	t	
						VBZ	VBZ-FP
26 1.02	M 6	20 .79	7 .28	16 .63	6 .24	9 .35	8 .31
26 1.02	M 8	20 .79	9 .35	16 .63	6 .24	9 .35	8 .31

Specification

- Phenolic plastic
 - Temperature resistant up to 302 °F (150 °C)
 - Black, shiny finish
- Tapped insert
 - Brass, molded-in
- RoHS compliant

Information

For slip-free fastening and clamping, these VBZ and VBZ-FP knurled nuts are an excellent economical choice.

see also...

- Knurled Screws VPZ (with Steel Threaded Stud)

How to order (Blind tapped insert) 1 2 VBZ-26-M8	1	Handle diameter d ₁
	2	Thread d ₂
How to order (Through tapped insert) 1 2 VBZ-FP-26-M6	1	Handle diameter d ₁
	2	Thread d ₂

1.1
1.2
1.3
1.4
2.1
2.2
2.3
2.4

