



Universal table

Dimensions in: millimeters - inches

¹ d ₁	² d ₂ Pilot Hole	d ₃	d ₄	l ₃	l ₄	l ₅	b	l ₂	l ₁	d ₅
75 2.95	P 4	24 .94	34 1.34	11 .43	22 .87	43 1.69	20 .79	19 .75	39 1.54	17 .67
90 3.54	P 6	32 1.26	44 1.73	12 .47	25 .98	43 1.69	20 .79	22 .87	42 1.65	17 .67

Specification

- Plastic
Duroplast (Phenolic)
- Temperature resistant up to 266 °F (130 °C)
- Black, glossy finish
- Hub bushing
Zinc plated steel, molded-in
- Revolving handles
- Plastic, Duroplast
Black, glossy finish
- Spindle
Steel, zinc plated
- Both dimensions, inch and metric, are interchangeable
- RoHS compliant

Information

VUM five-lobed control knobs with revolving handle are ideally suited for light-medium duty adjusting or clamping applications.

see also...

- Five-Lobed Control Knobs VUA
- Five-Lobed Control Knobs VU

On request

- Other modifications such as inch and metric blind bores, threads, etc.

How to order ¹ ² VUM-75-P	1 Knob diameter d ₁
	2 Pilot hole d ₂