



Universal table

Dimensions in: millimeters - inches

¹ d ₁	² d ₂ Pilot hole	d ₃	d ₄	d ₅	b	l ₁	l ₂	l ₃	l ₄	l ₅
75 2.95	P 4	24 .94	34 1.34	17 .67	20 .79	39 1.54	19 .75	11 .43	22 .87	43 1.69
90 3.54	P 6	32 1.26	44 1.73	17 .67	20 .79	42 1.65	22 .87	12 .47	25 .98	43 1.69

Specification

- Plastic
Duroplast (Phenolic)
- Temperature resistant up to 266 °F (130 °C)
- Black, glossy finish
- Hub bushing
Steel, zinc plated, molded-in
- Revolving handles
- Plastic, Duroplast
Black, glossy finish
- Threaded spindle
Steel, zinc plated
- RoHS compliant

Information

VUM five-lobed control knobs with revolving handle are ideally suited for light-medium duty adjusting or clamping applications.

see also...

- Five-Lobed Control Knobs VUA
- Five-Lobed Control Knobs VU

On request

- Other modifications such as inch and metric blind bores, threads, etc.

<p>How to order</p> <p>¹ ²</p> <p>VUM-75-P4</p>	1 Knob diameter d ₁
	2 Pilot hole d ₂