



Inch table

Dimensions in: inches - millimeters

d ₁	d ₂ Thread	d ₃	l ₁	l ₂	l ₃	Spring Load ≈ initial	end
.155 3.9	1/4 x 20	.47 11.9	.57 14.5	.19 4.8	.31 7.9	.50 lbf 2.22 N	2.00 lbf 8.90 N
.250 6.4	3/8 x 16	.61 15.5	.82 20.8	.28 7.1	.44 11.2	.75 lbf 3.33 N	3.00 lbf 13.34 N
.312 7.9	1/2 x 13	.84 21.3	1.06 26.9	.38 9.7	.56 14.2	1.00 lbf 4.45 N	4.00 lbf 17.8 N
.375 9.5	5/8 x 11	1.06 26.9	1.31 33.3	.44 11.2	.69 17.5	1.12 lbf 5.0039 N	5.00 lbf 22.24 N

Specification

- Plunger Body
12L14 steel, zinc plated finish
- Plunger pin
Case hardened steel, zinc plated finish
- Pull ring
Spring steel, zinc plated finish

Information

Ideal for applications with limited space.

On request

- Locking patch

<p>How to order (Stubby Hand Retractable Spring Plunger)</p> <p>1 2 3</p> <p>SPRP-0.155-1/4X20-ST</p>	1 d ₁
	2 Thread d ₂
	3 Material

3.1
3.2
3.3
3.4
3.5
3.6
3.7
3.8
3.9

