



**Inch table**

Dimensions in: inches - millimeters

d <sub>1</sub>	d <sub>2</sub> Thread	d <sub>3</sub>	l <sub>1</sub>	l <sub>2</sub>	l <sub>3</sub>	Spring Load ≈ initial	end
.155 3.9	1/4 x 20	.47 11.9	.57 14.5	.19 4.8	.31 7.9	.50 lbf 2.22 N	2.00 lbf 8.90 N
.250 6.4	3/8 x 16	.61 15.5	.82 20.8	.28 7.1	.44 11.2	.75 lbf 3.33 N	3.00 lbf 13.34 N
.312 7.9	1/2 x 13	.84 21.3	1.06 26.9	.38 9.7	.56 14.2	1.00 lbf 4.45 N	4.00 lbf 17.8 N
.375 9.5	5/8 x 11	1.06 26.9	1.31 33.3	.44 11.2	.69 17.5	1.12 lbf 5.0039 N	5.00 lbf 22.24 N

**Specification**

- Plunger Body  
12L14 steel, zinc plated finish
- Plunger pin  
Case hardened steel, zinc plated finish
- Pull ring  
Spring steel, zinc plated finish

**Information**

Ideal for applications with limited space.

**On request**

- Locking patch

<p>How to order (Stubby Hand Retractable Spring Plunger)</p> <p><b>1</b> <b>2</b> <b>3</b></p> <p><b>SPRP-0.155-1/4X20-ST</b></p>	<b>1</b> d <sub>1</sub>
	<b>2</b> Thread d <sub>2</sub>
	<b>3</b> Material

3.1  
3.2  
3.3  
3.4  
3.5  
3.6  
3.7  
3.8  
3.9

