
Lashing Straps

Stainless Stee Fasteners, Strap Plastic, Fixed Length



Metric



SS Stainless Steel

3 Type

- **AA** 2 flat screw-on plates
- **AD** Flat screw-on plate, suspension plate and screw-on hook
- **BB** 2 45° screw-on plates
- **BD** 45° screw-on plate, suspension plate and screw-on hook
- **BF** 45° screw-on plate, 45° screw-on plate for locking

Metric table

Dimensions in: millimeters / inches

1 b_1	2 l_1 ≈					b_2	b_3	d_1	d_2	h_1	h_2	l_2	l_3	s
25 0.98	250 9.84	400 15.75	600 23.62	1000 39.37	1500 59.06	34 1.34	22 0.87	5.3 0.21	22.5 0.89	11.7 0.46	8 0.31	8 0.31	17 0.67	1.5 0.06

Specification

Fasteners
Stainless steel AISI 304 — **NI**

Strap
Plastic, polyester
• Woven
• Black — ● **B**

RoHS

Technical Information	Page
Application Examples	QVX
Plastic Characteristics	QVX
Stainless Steel Characteristics	QVX

Lashing straps GN 1112 have a fixed length. When used as a holding strap, they limit the opening angle of doors and covers or serve as bracing or gripping elements. Thanks to the fasteners permanently sewn onto the ends, the lashing straps can be securely screwed or riveted in place. Types AD and BD can be quickly and easily attached or detached thanks to the additional hook latch. Type BF can be compactly secured to the body of a latch by means of an external thread (e.g. GN 115) so that they require no further fastening. Lashing straps GN 1112 may not be used for lifting loads or for lashing.

How to order

GN 1112-25-600-BB-NI-B (1 2 3 4 5)

1	Width b_1
2	Length l_1
3	Type
4	Material
5	Color

⚠ WARNING: Cancer and Reproductive Harm — www.P65Warnings.ca.gov