
Lashing Straps

Stainless Stee Fasteners, Strap Plastic, Adjustable Length



Metric



SS Stainless Steel

3 Type

AA 2 flat screw-on plates
AD Flat screw-on plate, suspension plate and screw-on hook
BB 2 45° screw-on plates
BD 45° screw-on plate, suspension plate and screw-on hook

Metric table

Dimensions in: millimeters / inches

1 b_1	2 l_1 ≈ min.	l_1 ≈ max	b_2	b_3	d	h_1	h_2	l_2	s
25 0.98	250 9.84	410 16.14	34 1.34	22 0.87	5.3 0.21	11.7 0.46	8 0.31	8 0.31	1.5 0.06
25 0.98	400 15.75	710 27.95	34 1.34	22 0.87	5.3 0.21	11.7 0.46	8 0.31	8 0.31	1.5 0.06
25 0.98	600 23.62	1110 43.70	34 1.34	22 0.87	5.3 0.21	11.7 0.46	8 0.31	8 0.31	1.5 0.06

Specification

Fasteners (4: NI, 5)
Stainless steel AISI 304 — NI

Strap
Plastic, polyester
• Woven
• Black — B

RoHS

Technical Information	Page
Application Examples	QVX
Plastic Characteristics	QVX
Stainless Steel Characteristics	QVX

Lashing straps GN 1113 can be adjusted to any length by means of the bar buckle. When used as a holding strap, they limit the opening angle of doors and covers or serve as bracing or a carry strap.
Thanks to the fasteners permanently sewn onto the ends, the lashing straps can be securely screwed or riveted in place. Types AD and BD can be quickly and easily attached or detached thanks to the additional hook latch.
Lashing straps GN 1113 may not be used for lifting loads or for lashing.

see also...	Page
GN 1110 Lashing Straps (Single-Part)	QVX
GN 1111 Lashing Straps (Multi-Part)	QVX
GN 1112 Lashing Straps (Fixed Length)	QVX

How to order

GN 1113-25-600-BB-NI-B (1 2 3 4 5)

1	Width b_1
2	Length l_1
3	Type
4	Material
5	Color

⚠ WARNING: Cancer and Reproductive Harm — www.P65Warnings.ca.gov