
# Cam Latches with Hook

Stanless Steel, with Operating Elements





#### Metric





# **1** Туре

SG With hand knob KGN With wing knob HGN With lever SKN With wing knob STN With T-handle

# 3 Hook version

H1 Pivoting radius R=28mm

## Identification no.

1 Without latch bracket

2 With latch bracket

## Metric table



Dimensions in: millimeters / inches

Hook distance A	d		h	
	Type SG / KGN / HGN	Type SKN / STN	Type SG / KGN / HGN	Type SKN / STN
18	28	32	4	6
0.71	1.10	1.26	0.16	0.24

see also...

\* Dimensions of the latch bracket, see page XYZ

## **Specification**



## Cam latch housing Stainless steel

• AISI 303 for type SG / KGN / HGN

• AISI 316 for type SKN / STN

#### Operating elements

- Stainless steel AISI 304 for type SG Sheet metal drawn / Hub welded
- Stainless steel AISI CF-8 for type KGN / HGN
- Stainless steel AISI 316 for type SKN / STN

#### Other parts

Stainless steel AISI 304

**RoHS** 

## On request

- · Cam latches with other hook distance A
- · Hook with other pivoting radius R

Cam latches with hook GN 115.8 and latch bracket are mainly used for sliding doors and flaps. The latching action is in a radial direction to the axis of rotation, resulting in a wide variety of different uses.

The latches GN 115.8 are supplied with loosely enclosed hook.

32

GN 115.8 Cam Latches with Hook (Zinc Die-Cast Housing, with Operating Elements)	QVX
Technical Information	
Construction and Assembly Instructions	QVX
List of Cam Latch / Cam Lock Types	QVX
IP Protection Classes	QVX
Stainless Steel Characteristics	QVX



Page