



**SS** Stainless Steel

**1 Type**

- DK** With triangular spindle
- VK7** With square spindle
- VK8** With square spindle
- VDE** With double bit

**Metric table**

**2**

Dimensions in: millimeters - inches

Latch arm distance <b>A</b>								
6	10	14	18	20	22	24	26	28
0.24	0.39	0.55	0.71	0.79	0.87	0.94	1.02	1.10

**Specification**

**3**

- Lock housing  
Stainless steel AISI 316Ti **A4**
- Latch arm  
Stainless steel AISI 316
- Other parts  
Stainless steel AISI 316
- Protection class IP 66
- IP Protection Classes → page QVX
- Stainless Steel Characteristics → page QVX
- RoHS

**Accessory**

- Socket Keys GN 119.2 → page QVX
- Protective Caps GN 120 → page QVX
- Finger Grip Opening Handles GN 120.1 → page QVX
- Protective Guide Plates GN 120.2 → page QVX
- Internal Cabinet Handles GN 120.3 → page QVX
- Sheet Metal Punches GN 123 → page QVX

**On request**

- Other operations

**Information**

Cam latches GN 115 lock by a turning operation limited to 90° which moves the latch arm in the locked position behind the door frame. The bevels of the latch arm ease the closing of the door. Thanks to the stainless steel materials used, the latches are optimally suited for use in corrosive environments. Latch arms are available with different bend angles to cover a latch arm distance A from 6 to 28 mm. Product comes supplied with a loosely enclosed latch arm.

see also...

- Construction and Assembly Instructions → page QVX
- List of Cam Latch / Cam Lock Types → page QVX
- Cam Latches GN 115 (Stainless Steel, Operation with Socket Keys, Protection Class IP 69k) → page QVX
- Cam Latches GN 115 (Zinc Die-Cast, Operation with Socket Key) → page QVX
- Cam Locks GN 115 (Stainless Steel) → page QVX

**How to order**

**GN 115-DK-18-A4**

<b>1</b>	Type
<b>2</b>	Latch arm distance A
<b>3</b>	Material