



**SS** Stainless Steel

**Metric table**



Dimensions in: millimeters - inches

d <sub>1</sub>	d <sub>2</sub>	d <sub>3</sub>	s	For DIN 7991 / DIN ISO 2009 countersunk screws with thread size
16 0.63	4.3 0.17	8 0.31	3 0.12	M 4
20 0.79	4.3 0.17	8 0.31	3 0.12	M 4
22 0.87	5.3 0.21	10 0.39	3.5 0.14	M 5
25 0.98	5.3 0.21	10 0.39	3.5 0.14	M 5
28 1.10	5.3 0.21	10 0.39	3.5 0.14	M 5
32 1.26	6.4 0.25	12 0.47	4 0.16	M 6
36 1.42	6.4 0.25	12 0.47	4 0.16	M 6
40 1.57	6.4 0.25	12 0.47	5 0.20	M 6
45 1.77	6.4 0.25	12 0.47	6 0.24	M 6
52 2.05	6.4 0.25	12 0.47	6 0.24	M 6

**Specification**

- **GN 184**  
Steel  
- Turned  
- Blackened finish
- **GN 184.5**  
Stainless steel AISI 303  
- Turned  
- Matte shot-blasted finish
- *Stainless Steel Characteristics* → page 2143
- **RoHS compliant**

**Information**

GN 184 and GN 184.5 countersunk washers are retained to the face of the shaft end with DIN 7991 / DIN ISO 2009 countersunk screws, forming a clean-look end cap.

A typical application example would be the retention of a handwheel with keyway to a shaft.

How to order (Steel)	1	Outer diameter d <sub>1</sub>
<b>GN 184-28</b>		

How to order (Stainless steel)	1	Outer diameter d <sub>1</sub>
<b>GN 184.5-36</b>		