



**SS** Stainless Steel

**Metric table**



Dimensions in: millimeters - inches

d <sub>1</sub>	d <sub>2</sub>	d <sub>3</sub>	s <sub>1</sub>	s <sub>2</sub>	For DIN 7991 / DIN ISO 2009 countersunk screws with thread size
18 <i>0.71</i>	4.3 <i>0.17</i>	8.5 <i>0.33</i>	3 <i>0.12</i>	0.8 <i>0.03</i>	M 4
20 <i>0.79</i>	5.3 <i>0.21</i>	10.5 <i>0.41</i>	3.5 <i>0.14</i>	1 <i>0.04</i>	M 5
22 <i>0.87</i>	6.4 <i>0.25</i>	12.6 <i>0.50</i>	4 <i>0.16</i>	1 <i>0.04</i>	M 6
26 <i>1.02</i>	8.4 <i>0.33</i>	16.8 <i>0.66</i>	5 <i>0.20</i>	1 <i>0.04</i>	M 8

**Specification**



- Washer body  
Stainless steel AISI 303  
Matte shot-blasted finish **NI**
- Disk  
Plastic, white  
Technopolymer (Polyamide PA)
- Plastic Characteristics* → page 2135
- Stainless Steel Characteristics* → page 2143
- RoHS compliant

**Information**

GN 185 countersunk washers are used for shrouding screw joints when a visually appealing finish is desired.  
The plastic disks avoid damage to finished surfaces and are included with the washer.

<p>How to order</p> <p><b>GN 185-18-NI</b></p>	1	Outer diameter d <sub>1</sub>
	2	Material

3.1  
3.2  
3.3  
3.4  
3.5  
3.6  
3.7  
3.8  
3.9  
3.10

