



4 Type

- L Clamping direction left turn
- R Clamping direction right turn

Metric table

Dimensions in: millimeters - inches

² d ₁	³ d ₂ H8 Bore		d ₃	l ₁ ≈	l ₂	l ₃	l ₄
35 1.38	B 8	B 10	18 0.71	15 0.59	7 0.28	7 0.28	3 0.12
65 2.56	B 12	-	23 0.91	20 0.79	10 0.39	7 0.28	5 0.20
80 3.15	B 16	-	27 1.06	24 0.94	12 0.47	9 0.35	6 0.24

Specification

- Steel, sintered **SM**
- Black steam oxidized finish
- ISO Fundamental Tolerances → page 2129
- RoHS compliant

Information

GN 218 cam latches are available as right or left hand models, dependent on how the door should be latched (i.e. in a right or left hand mode).

In addition a circlip, spring or other plastic part can be built in between the door and the latch. This will stiffen the latching action and also simplify assembly.

see also...

- Door Cam Latches EN 118 (Complete Kits) → www.jwwinco.com

How to order	1 Material
¹ ² ³ ⁴ GN218-SM-35-B10-L	2 Outside diameter d ₁
	3 Bore d ₂
	4 Type

3.1
3.2
3.3
3.4
3.5
3.6
3.7
3.8
3.9
3.10

