



Metric table

Dimensions in: millimeters - inches

¹ d ₁	² d ₂ Thread	³ l ₁	d ₃	l ₂ min.	l ₃ ±0.5	l ₄ ≈
34 1.34	M 10	67 2.64	19 0.75	40 1.57	8 0.31	24 0.94
34 1.34	M 10	86 3.39	20 0.79	48 1.89	7 0.28	25 0.98

Specification

- Plastic
Duroplast (Phenolic PF)
 - Temperature resistant up to 230 °F (110 °C)
 - Black, shiny finish
 - Molded-in thread
- *Plastic Characteristics* → page QVX
- **RoHS compliant**

Information

When using EN 219 tapered knobs, make sure that the threaded end of the shaft is long enough and seats flush inside the threaded hole of the handle, otherwise the plastic may break under excessive stress.

How to order ¹ ² ³ EN 219-34-M10-67	1 Handle diameter d ₁
	2 Thread d ₂
	3 Handle length l ₁