



2 Bore code

- B** Without keyway
- K** With keyway
- V** With square

Metric table

Dimensions in: millimeters - inches

1 d_1	3 d_2 Bore H7 Square H11	d_3	d_4	h_1	h_2	$h_3 \approx$	Length $l \approx$
25 0.98	8 0.315	6 0.24	16 0.63	14 0.55	5 0.20	35 1.38	45 1.77
32 1.26	10 0.394	8 0.31	20 0.79	18 0.71	6.5 0.26	48 1.89	62 2.44
40 1.57	12 0.472	10 0.39	30 1.18	22 0.87	8.5 0.33	77 3.03	95 3.74
52 2.05	16 0.630	14 0.55	40 1.57	28 1.10	11 0.43	96 3.78	136 5.35

Specification

- Hub / arm
Steel, blackened finish
- Ball knob DIN 319 → page QVX
Plastic
Duroplast (Phenolic PF)
Black, shiny finish
- Keyways *WN / DIN 6885* → page QVX
- ISO Fundamental Tolerances → page QVX
- RoHS compliant

On request

- Special inch and metric bores or threads

Information

- see also...
- Control Levers GN 750 (Steel, Blackened Finish) → page QVX

<p>How to order</p> <p>GN 223-32-B10</p>	1 Diameter d_1
	2 Bore code
	3 Bore d_2 (Keyway, Square)