



SS Stainless Steel

Metric table

¹ d ₁	² Length l ±0.25	d ₂	h
8 0.31	30 1.18	12 0.47	26 1.02
10 0.39	40 1.57	15 0.59	31 1.22

Dimensions in: millimeters - inches

Specification

- **GN 224.1**
Steel, chrome-plated finish
Location disks
Zinc die-cast, nickel-plated finish

³ CR

- **GN 224.5**
Stainless steel AISI 304
Matte shot-blasted finish
Location disks
Stainless steel AISI 303

- [Stainless Steel Characteristics](#) → page QVX
- [RoHS compliant](#)

On request

- Various metric size fasteners and kit packaging

Information

GN 224.1 and GN 224.5 finger grip handles are supplied with two location disks. They guarantee a perfect location even with oversize mounting holes in the cabinet. The disks are supplied loose.

How to order (Steel) ¹ ² ³ GN 224.1-8-30-CR	1 Handle diameter d ₁
	2 Length l
	3 Finish
How to order (Stainless steel) ¹ ² GN 224.5-10-40	1 Handle diameter d ₁
	2 Length l