



**Metric table**

Dimensions in: millimeters - inches

1 d <sub>1</sub>	2 Length l		3 d <sub>2</sub> Bore	d <sub>3</sub>	h
	Nominal dimension	Actual dimension			
9 0.35	30 1.18	29.5 1.16	B 3.5	12 0.47	27 1.06
10 0.39	40 1.57	39.5 1.56	B 3.5	15 0.59	33.5 1.32

**Specification**

- Plastic  
Technopolymer (Polyamide PA)  
Temperature resistant up to 212 °F (100 °C)
- Color (matte finish):
  - SW Black, RAL 9005
  - OR Orange, RAL 2004
  - GR Gray, RAL 7035
  - RT Red, RAL 3000
  - WS White, RAL 9002
- Strength Values → page 2081
- Plastic Characteristics → page 2135
- RoHS compliant

**Information**

EN 224.3 finger grip handles with bore hole B 3.5 mm are intended for mounting with self-tapping screws, such as DIN ISO 7049 pan head tapping screws of thread size ST 4.2 mm.

see also...

- Finger Grip Handles GN 224.1 (Steel) → [www.jwwinco.com](http://www.jwwinco.com)
- Finger Grip Handles GN 224.5 (Stainless Steel) → [www.jwwinco.com](http://www.jwwinco.com)

How to order  1 2 3 4 <b>EN 224.3-10-40-B3.5-SW</b>	1	Handle diameter d <sub>1</sub>
	2	Length l
	3	Bore d <sub>2</sub>
	4	Color

1.1 1.2 1.3 1.4 2.1 2.2 2.3 2.4