



4 Sensitivity
30 Angular minutes,
bubble moves by 2 mm

5 Type
A With smooth reference surface
B With threaded stud for mounting

Metric table

Dimensions in: millimeters - *inches*

d ₁	d ₂	d ₃ Thread	h ₁	h ₂	h ₃
14 .55	10 .39	M 4	9.5 .37	7.7 .30	5 .20
20 .79	14 .55	M 5	13 .51	13 .51	6 .24
30 1.18	21 .83	M 6	15 .59	15 .59	7.5 .30

Specification



- Housing
Aluminum
Anodized finish, natural color **ALN**
Anodized finish, black **ALS**
- Spirit level element
Glass plastic body
- Filling
Colorless transparent **K**
- Casting compound
Mineral-based
- RoHS compliant

On request

- Green transparent filling
- Other sensitivities
- Housing in brass or stainless steel

Information

GN 2279 bull's eye spirit levels are used to check the horizontal position of jigs, machines, devices, appliances and instruments.

Type A is suggested if the spirit level is to be used as a tool, e.g. at different measuring points.

The spirit levels are aligned in relation to the reference surface so that the bubble is centrally located inside the marking ring when the horizontal position of the contact surface is achieved.

see also...

• *General Information on Bull's Eye Spirit Levels, Screw-On Spirit Levels, and Cross Spirit Levels* → page QVX

How to order

GN 2279-ALS-20-K-30-A

1	Color
2	Outside diameter d ₁
3	Filling
4	Sensitivity
5	Type