



**3 Type**

- AF** Exterior hinge leaf
- AN** Exterior hinge leaf, with positioning guide
- IF** Interior hinge leaf
- IN** Interior hinge leaf, with positioning guide

**4 Identification**

- A** Without bores
- C** With countersunk holes

**Metric table**

Dimensions in: millimeters - inches

1		2				d <sub>1</sub>	d <sub>2</sub>	d <sub>3</sub>	l <sub>3</sub>	l <sub>4</sub>	m <sub>1</sub>		m <sub>2</sub>	m <sub>3</sub>	m <sub>4</sub>	n - 0.3	s <sub>1</sub>	s <sub>2</sub>	
l <sub>1</sub>	Type AF Type AN	Type IF Type IN	l <sub>2</sub>								Type AF Type AN	Type IF Type IN							
43	50		40	80	250*	400*	6.6	14	8	36	43	20.4	27.5	50	50	150	8	3.5	6.5
1.69	1.97		1.57	3.15	9.84	15.75	0.26	0.55	0.31	1.42	1.69	0.80	1.08	1.97	1.97	5.91	0.31	0.14	0.26

\*Only available in Types AF and IF

**Specification**

- Aluminum
- Anodized finish, natural color
- RoHS compliant



**EL**

**Accessory**

- Hinge pin sets GN 2290 → page 1352

**On request**

- Other lengths and hole spacings
- Other finishes

**Information**

GN 2291 hinge leafs can be combined with GN 2290 hinge pin sets into individualized hinge versions. Special lengths can be created for a hinge leaf length of  $l_2 \geq 250$  mm, since the increased mounting hole distance from the end allows shortening the hinge leaf.

see also...

- Product Family Standard Parts for Profile Systems → page 18
- Double Leaf Hinges GN 2292 (with Positioning Guide) → page 1409
- Double Leaf Hinges GN 2294 → page 1410
- Triple Leaf Hinges GN 2295 → page 1350

How to order	
1	Width l <sub>1</sub>
2	Length l <sub>2</sub>
3	Type
4	Identification
5	Finish

**GN 2291-43-80-AF-A-EL**