



SS Stainless Steel

Metric table

2

Dimensions in: millimeters - inches

l ₂	b	d	l ₁	m ₁	m ₂	s	Suitable for hinges with hole spacing m ₂									
							GN 235	GN 387	EN 337.1	GN 437	GN 7231	GN 7233	GN 7237	GN 237	EN 237.1	GN 237.3
30 1.18	9 0.35	M 4	30 1.18	18 0.71	18 0.71	3 0.12	-	-	-	-	x	-	-	-	-	-
40 1.57	12 0.47	M 5	40 1.57	25 0.98	25 0.98	3 0.12	x	-	-	x	-	-	-	-	-	-
50 1.97	15 0.59	M 6	50 1.97	30 1.18	30 1.18	4 0.16	x	-	-	x	x	-	-	-	-	-
60 2.36	18 0.71	M 8	60 2.36	36 1.42	36 1.42	4 0.16	x	-	-	x	x	x	-	-	-	-

Specification

1

3

- Stainless steel AISI 304 **NI**
Matte, tumbled finish **MT**
- *Stainless Steel Characteristics* → page 2143
- **RoHS compliant**

Information

GN 2372 spacer plates are designed as accessories for several hinge variations, eliminating the need for additional threads, nuts, and washers for mounting.

There is no need for the time-consuming pre-assembly of the above components or for counterholding during tightening or loosening. Mounted to the top side of the hinge, the plate offers entirely new design options.

see also...

- *Mounting Plates with Threaded Studs GN 2376* → page 1382
- *Limit Stops GN 2374* → page 1336
- *Spacer Plates GN 7247.2* → page 1396
- *Spacer Plates with Tapped Holes GN 7247.4* → page 1397
- *Mounting Plates with Threaded Studs GN 7247.6* → page 1398

How to order

GN 2372-NI-40-MT

- 1 **Material**
- 2 **Length l₂**
- 3 **Finish**

3.1
3.2
3.3
3.4
3.5
3.6
3.7
3.8
3.9
3.10

