



**Metric table**

Dimensions in: millimeters - inches

<sup>2</sup> l <sub>2</sub>	<sup>3</sup> w ≈ Angle of rotation in °	b	d	h	l <sub>1</sub>	m <sub>1</sub>	m <sub>2</sub>	s
40 1.57	150	12 0.47	5.3 0.21	7.8 0.31	40 1.57	25 0.98	25 0.98	3.5 0.14
50 1.97	150	15 0.59	6.3 0.25	9.2 0.36	50 1.97	30 1.18	30 1.18	4 0.16
60 2.36	150	18 0.71	8.3 0.33	10.9 0.43	60 2.36	36 1.42	36 1.42	5 0.20

**Specification**

- Body  
Steel precision casting **ST**  
Zinc plated, powder coated  
Black, RAL 9005, textured finish **●SW**
- Elastomer element  
- Rubber NBR (Perbunan®)  
- Temperature resistant up to 248 °F (120 °C)  
- Hardness 85±5 shore A
- *Plastic Characteristics* → page 2135
- **RoHS compliant**

**Information**

GN 2374 limit stops are designed as accessories for the GN 237, EN 237.1, GN 337 and EN 337.1 series of hinges. The limit stops are attached on top of the hinge using screws when mounting the hinge itself. The elastomer element limits the angle of rotation to the value w.

They are mainly used for lighter traps and gates, or when the limit stop is not expected to be exposed to dynamic loads.

see also...

- *Hinges GN 237* → page 1330
- *Hinges EN 237.1* → page 1334
- *Lift-Off Hinges GN 337* → page 1407
- *Lift-Off Hinges EN 337.1* → page 1408

How to order

<sup>1</sup> <sup>2</sup> <sup>3</sup> <sup>4</sup>  
**GN 2374-ST-40-150-SW**

<sup>1</sup>	Material
<sup>2</sup>	Length l <sub>2</sub>
<sup>3</sup>	Angle of rotation w
<sup>4</sup>	Finish