



Metric table

| | | Dimensions in: millimeters |
|------------------|------------------|---------------------------------------------------|
| 1 | 2 | |
| A/F ₁ | A/F ₂ | Suitable for cam roller carriages and cam rollers |
| 8 | 8 | GN 2424, GN 2426 |
| 13 | 15 | GN 2424, GN 2494, GN 2426, GN 2496 |

Specification

- Steel, zinc plated
- RoHS compliant

Information

see also...

- *Cam Roller Carriages GN 2424 (Aluminum / Steel) → page QVX*
- *Cam Roller Carriages GN 2494 (Stainless Steel) → page XYZ*
- *Cam Rollers GN 2426 (Steel) → page XYZ*
- *Cam Rollers GN 2496 (Stainless Steel) → page XYZ*

| | | |
|--------------------------------------|----------|-------------------------------------|
| How to order GN 2424.1-8-8 | 1 | Width across flats A/F ₁ |
| | 2 | Width across flats A/F ₂ |

3.1
3.2
3.3
3.4
3.5
3.6
3.7
3.8
3.9
3.10

