



Metric table

Dimensions in: millimeters - inches

¹ d ₁ Bore for sensor	² b Swivel width	d ₂	d ₃	Length l	m ₁	m ₂	t ₁	t ₂	x ₁	x ₂	y ₁	y ₂
B 18	40 1.57	50 1.97	6.5 0.26	52.5 2.07	32.5 1.28	30 1.18	10 0.39	7 0.28	60 2.36	42 1.65	60 2.36	42 1.65
B 30	40 1.57	50 1.97	6.5 0.26	52.5 2.07	32.5 1.28	30 1.18	10 0.39	7 0.28	60 2.36	42 1.65	60 2.36	42 1.65

Specification

- Aluminum
- Powder coated
- Black, RAL 9005, textured finish ● SW
- RoHS compliant

On request

- Stainless steel version

Information

GN 272.4 sensor holders accept sensors with external thread via the bore d₁.

see also...

- *Sensor Holders GN 271.4* → page QVX
- *Attachment Mounting Clamps GN 478* → page QVX

How to order ¹ ² ³ GN 272.4-B30-40-SW	1 Bore d ₁
	2 Swivel width b
	3 Finish

3.1
3.2
3.3
3.4
3.5
3.6
3.7
3.8
3.9
3.10