



Dimensions in: millimeters - inches

<b>1</b> d <sub>1</sub> Bore Clamp connector	<b>2</b> d <sub>2</sub> Bore				<b>3</b> Length l
18 0.71	B 12	B 14	B 15	B 16	29 1.14
30 1.18	B 20	B 25	-	-	45 1.77

**Specification**

- Plastic  
Technopolymer (Polyamide PA)
  - Glass fiber reinforced
  - Temperature resistant up to 212 °F (100 °C)
  - Black, RAL 9005, matte finish ● **SW**
  - Gray, RAL 7040, matte finish ○ **GR**
- Load Rating Information → page QVX
- Plastic Characteristics → page QVX
- RoHS compliant

**Information**

Adapter bushings EN 290 can be used to reduce the bore diameter of plastic clamp connectors for clamping smaller diameters.

Due to the affixed swivel limiting stop, the adapter bushing cannot rotate or slide inside the clamp connector.

see also...

- Plastic Clamp Connectors → starting from page XYZ
- Construction Tubes GN 990 → page QVX

How to order	<b>1</b> Bore d <sub>1</sub>
<b>1</b> <b>2</b> <b>3</b> <b>4</b>	<b>2</b> Bore d <sub>2</sub>
<b>EN 290-30-B20-45-SW</b>	<b>3</b> Length l
	<b>4</b> Color