



Metric



3 Type

A Mounting from the back (tapped blind hole)

Metric table

Dimensions in: millimeters / inches

1		2					4									
d ₁	Length l					d ₂	b ₁	b ₂	b ₃	b ₄	h ₁	h ₂	t min.			
28 1.10	242 9.53	292 11.50	392 15.43	492 19.37	592 23.31	M 8	25 0.98	14 0.55	50 1.97	66 2.60	50 1.97	66 2.60	15 0.59			

Specification

Handle tube

- Aluminum, wall thickness 1.5 mm
- Powder coated
 - Black, RAL 9005, textured finish
- Handle legs black
- Anodized finish, natural color
 - Handle legs black
- Anodized finish, natural color
 - Handle legs silver

- **SW**
- **ELS**
- **ELG**

Handle legs

- Zinc die-cast
- Powder coated, textured finish
 - Black, RAL 9005 for SW / ELS
 - Silver, RAL 9006 for ESG

Cover

- Plastic
 - Black, matte finish for SW / ELS
 - Light gray, matte finish for ELG

RoHS

On request

- Special tube lengths

The spacing of the attachment holes of the tubular handles GN 333.2 is adjustable. Additional handle legs can be added for very long tubular handles.

Individual handle legs for tubular handles Ø 28 (type A) are available under GN 333.8.

Tubular handles GN 333.2 are supplied unassembled.

see also...

	Page
GN 333 Tubular Handles (with Fixed Handle Legs)	QVX
GN 333.3 Tubular Handles (with Straight Movable Handle Legs)	QVX
GN 930 Handle Tubes	QVX

Technical Information

Load Capacity Information	QVX
---------------------------	-----

Accessory

GN 333.8 Angled Handle Legs	QVX
------------------------------------	-----

How to order

1	Handle diameter d ₁
2	Length l
3	Type
4	Finish

GN 333.2-28-492-A-SW

1.1
1.2
1.3
1.4
2.1
2.2
2.3
2.4

