



Inch | Metric



Inch table

Dimensions in: inches / millimeters

1		2						a	b ₂	d	h ₁	h ₂	l ₂	t min.
b ₁	l ₁ ±0.02													
1.42	8.00	10.00	12.00	16.00	20.00	24.00	0.94	0.87	5/16 x 18	2.24	2.80	1.57	0.59	
36.1	203.2	254	304.8	406.4	508	609.6	23.9	22.1		56.9	71.1	39.9	15	

Metric table

Dimensions in: millimeters / inches

1		2						a	b ₂	d	h ₁	h ₂	l ₂	t min.	
b ₁	l ₁ ±0.5														
36	200	250	300	350	400	500	600	800	24	22	M 8	57	71	40	15
1.42	7.87	9.84	11.81	13.78	15.75	19.69	23.62	31.50	0.94	0.87		2.24	2.80	1.57	0.59

Specification

Handle tube

Aluminum

• Powder coated

Black, RAL 9005, textured finish

Handle legs black

● **SW**

• Anodized finish, natural color

Handle legs black

● **EL**

• Anodized finish, natural color

Handle legs silver

● **ES**

Handle legs

Zinc die-cast

Powder coated, textured finish

• Black, RAL 9005 for SW / EL

• Silver, RAL 9006 for ES

Cover

Plastic, light gray

RoHS

On request

Special tube lengths other than listed

Oval tubular handles GN 334 are attractive in design and highly stable.

Tube and handle legs are secured together with self-tapping screws and do not require any further machining or processing steps allowing even small quantities of special lengths to be manufactured. Screw heads are covered with plastic cover caps to provide a clean and finished look.

see also...

GN 333.1 Tubular Handles Page **QVX**

GN 334.1 Oval Tubular Handles (Mounting from the Operator's Side) Page **QVX**

GN 335 Oval Tubular Handles Page **QVX**

Technical Information

Load Capacity Information Page **QVX**

How to order (Inch)

GN 334-1.42-8.00-EL

- 1 Handle diameter b₁
- 2 Length l₁
- 3 Finish

How to order (Metric)

GN 334-36-200-EL

- 1 Handle diameter b₁
- 2 Length l₁
- 3 Finish

1.1
1.2
1.3
1.4
2.1
2.2
2.3
2.4

