



Inch table

Dimensions in: inches - *millimeters*

¹ b ₁	² l ₁ ±0.02	a	b ₂	d Thread	h ₁	h ₂	l ₂	t min.					
1.42 36.1	8.00 203.2	10.00 254.0	12.00 304.8	16.00 406.4	20.00 508.0	24.00 609.6	0.94 23.9	0.87 22.1	5/16 x 18	2.24 56.9	2.80 71.1	1.57 39.9	0.59 15.0

Metric table

Dimensions in: millimeters - *inches*

¹ b ₁	² l ₁ ±0.5	a	b ₂	d Thread	h ₁	h ₂	l ₂	t min.							
36 1.42	200 7.87	250 9.84	300 11.81	350 13.78	400 15.75	500 19.69	600 23.62	800 31.50	24 0.94	22 0.87	M 8	57 2.24	71 2.80	40 1.57	15 0.59

Specification

- Tube
Aluminum
- Handle legs
Zinc die-cast, powder coated
- Tube / handle legs ● **SW**
Powder coated
Black, RAL 9005, textured finish
- Tube ● **EL**
Anodized finish, natural color
Handle legs
Black, RAL 9005, textured finish
- Tube ● **ES**
Anodized finish, natural color
Handle legs
Silver, RAL 9006, textured finish
- Cover
Plastic, light gray
- Load Rating Information → page 2068
- RoHS compliant

Information

GN 334 oval tubular handles are attractive in design and highly stable. Tube and handle legs are secured together with self-tapping screws and do not require any further machining or processing steps allowing even small quantities of special lengths to be manufactured. Screw heads are covered with plastic cover caps to provide a clean and finished look.

On request

- Special tube lengths other than listed

<p>How to order</p> <p>GN 334-1.42-8.00-EL</p>	¹	Handle diameter b ₁
	²	Length l ₁
	³	Finish