



Inch | Metric



Inch table

1 2

Dimensions in: inches / millimeters

b ₁	l ₁ ±0.02							a	b ₂	d	h ₁	h ₂	h ₃	l ₂	l ₃	l ₄
1.42	8.00	10.00	12.00	16.00	20.00	24.00	0.94	1.50	0.335	2.24	2.83	0.20	0.57	0.30	1.61	
36.1	203.2	254	304.8	406.4	508	609.6	23.9	38.1	8.5	56.9	71.9	5.1	14.5	7.6	40.9	

Metric table

1 2

Dimensions in: millimeters / inches

b ₁	l ₁ ±0.5							a	b ₂	d	h ₁	h ₂	h ₃	l ₂	l ₃	l ₄	
36	200	250	300	350	400	500	600	800	24	38	8.5	57	72	5	14.5	7.5	41
1.42	7.87	9.84	11.81	13.78	15.75	19.69	23.62	31.50	0.94	1.50	0.335	2.24	2.83	0.20	0.57	0.30	1.61

Specification

3

Handle tube

Aluminum

- Powder coated
Black, RAL 9005, textured finish
- Handle legs black

● SW

- Anodized finish, natural color
Handle legs black

● EL

- Anodized finish, natural color
Handle legs silver

● ES

Handle legs

Zinc die-cast

- Powder coated, textured finish
• Black, RAL 9005 for SW / EL
- Silver, RAL 9006 for ES

Cover

Plastic, light gray

RoHS

On request

- Special tube lengths other than listed

Oval tubular handles GN 334.1 are attractive in design and highly stable.

Tube and handle legs are secured together with self-tapping screws and do not require any further machining or processing steps allowing even small quantities of special lengths to be manufactured. Screw heads are covered with plastic covers to provide a clean and finished look.

see also...

Page

GN 333.1 Tubular Handles

QVX

GN 334 Oval Tubular Handles (Mounting from the Back)

QVX

Technical Information

Load Capacity Information

QVX

How to order (Inch)

1 2 3

GN 334.1-1.42-8.00-SW

1	Handle diameter b ₁
2	Length l ₁
3	Finish

How to order (Metric)

1 2 3

GN 334.1-36-400-ES

1	Handle diameter b ₁
2	Length l ₁
3	Finish