



Inch table

1 2

Dimensions in: inches - millimeters

b ₁	l ₁ ±0.02							a	b ₂	d	h ₁	h ₂	h ₃	l ₂	l ₃	l ₄
1.42	8.00	10.00	12.00	16.00	20.00	24.00	0.94	1.50	0.335	2.24	2.83	0.20	0.57	0.30	1.61	
36.1	203.2	254.0	304.8	406.4	508.0	609.6	23.9	38.1	8.5	56.9	72.0	5.1	14.5	7.6	40.9	

Metric table

1 2

Dimensions in: millimeters - inches

b ₁	l ₁ ±0.5							a	b ₂	d	h ₁	h ₂	h ₃	l ₂	l ₃	l ₄	
36	200	250	300	350	400	500	600	800	24	38	8.5	57	72	5	14.5	7.5	41
1.42	7.87	9.84	11.81	13.78	15.75	19.69	23.62	31.50	0.94	1.50	0.33	2.24	2.83	0.20	0.57	0.30	1.61

Specification

3

- Tube
Aluminum
- Handle legs
Zinc die-cast, powder coated
- Tube / handle legs ● SW
Powder coated
Black, RAL 9005, textured finish
- Tube ● EL
Anodized finish, natural color
Handle legs
Black, RAL 9005, textured finish
- Tube ● ES
Anodized finish, natural color
Handle legs
Silver, RAL 9006, textured finish
- Cover
Plastic, light gray
- [Load Rating Information](#) → page 2068
- [RoHS compliant](#)

On request

- Special tube lengths other than listed

Information

GN 334.1 oval tubular handles are attractive in design and highly stable.

Tube and handle legs are secured together with self-tapping screws and do not require any further machining or processing steps allowing even small quantities of special lengths to be manufactured. Screw heads are covered with plastic covers to provide a clean and finished look.

see also...

- [Product Family Standard Parts for Profile Systems](#) → page 18
- [T-Nut Assemblies GN 965 \(for 30 / 40 mm T-Slot Profile Systems\)](#) → page 2048
- [T-Nut Assemblies GN 968 \(for 30 / 40 / 45 mm T-Slot Profile Systems\)](#) → page 2058

How to order

GN 334.1-1.42-8.00-SW

- | | |
|---|--------------------------------|
| 1 | Handle diameter b ₁ |
| 2 | Length l ₁ |
| 3 | Finish |

1.1
1.2
1.3
1.4
2.1
2.2
2.3
2.4