



- 2 Type**
- A Mounting from the back
 - B Mounting from the operator's side

Metric table



Dimensions in: millimeters - inches

$l_1 \pm 0.5$	d_1 Type A	d_2 Type B	b	h_1	h_2	l_2	l_3	s	t_1	t_2
132 5.20	M 8	8.5 0.33	23 0.91	52.5 2.07	13 0.51	173 6.81	113 4.45	9 0.35	12 0.47	8.5 0.33

Specification



- Plastic
Technopolymer (Polyamide PA)
- Glass fiber reinforced
- Temperature resistant up to 266 °F (130 °C)
- Black-gray, similar to RAL 7021, shiny finish
- Tapped inserts (Type A)
Brass
- Color of the cover cap (matte finish):

● DSG
● DOR
● DGR
● DGB
● DBL
● DRT
● DGN
- Strength Values → page 2081
- Plastic Characteristics → page 2135
- RoHS compliant

On request

- Various metric size fasteners and kit packaging

Information

The cover caps of GN 365 arch handles for type A are mounted on the handle, but supplied loose for type B.

<p>How to order</p> <p>EN 365-132-A-DSG</p>	1 2 3	1 Length l_1
		2 Type
		3 Color of the cover cap