



Metric table

Dimensions in: millimeters - inches

1	2	3									
d ₁	d ₂	Length l				d ₃	h ₁	h ₂	h ₃	S	
34 1.34	M 6	15 0.59	20 0.79	25 0.98	30 1.18	17 0.67	22 0.87	20 0.79	12 0.47	7 0.28	
34 1.34	M 8	15 0.59	20 0.79	25 0.98	-	17 0.67	22 0.87	20 0.79	12 0.47	7 0.28	
45 1.77	M 8	20 0.79	30 1.18	40 1.57	-	25 0.98	30 1.18	27 1.06	18 0.71	85 3.35	
45 1.77	M 10	30 1.18	-	-	-	25 0.98	30 1.18	27 1.06	18 0.71	85 3.35	
65 2.56	M 10	30 1.18	-	-	-	30 1.18	39 1.54	36 1.42	25 0.98	10 0.39	

Specification

- Three-lobed knob
Phenolic plastic
 - Temperature resistant up to 300 °F (150 °C)
 - Black, shiny finish
- Threaded stud
Steel, zinc plated
- Plastic Characteristics → page 2135
- RoHS compliant

Information

3P-P three-lobed knobs have an aesthetically pleasing shape, provide a comfortable grip and expand the range of clamping options.

Resistant to solvents, oils, grease and other chemical agents.

see also...

- Three-Lobed Knobs 3P-B (with Brass Tapped Insert) → page 651

<p>How to order</p> <p>1 2 3</p> <p>3P-P-45-M8-30</p>	1 Handle diameter d ₁
	2 Thread d ₂
	3 Length l