



4 Type

C With fastening set

Metric table

| 1 l_1 | 2 n_1 | 3 n_2 | d_1 | d_2 | d_3 | l_2 | l_3 | m_1 | m_2 | m_3 | m_4 | A/F_1 in mm | A/F_2 in mm | Grid size in mm |
|----------------|----------------|----------------|-------|-------|------------|--------------|--------------|--------------|--------------|-------------|------------|------------------|------------------|--------------------|
| 28 1.10 | 10 0.39 | 10 0.39 | M 8 | M 8 | - | 28 1.10 | 38 1.50 | 14.5 0.57 | 14.5 0.57 | 3.5 0.14 | 13 0.51 | 5 | 5 | 40 / 45 |
| 40 1.58 | 10 0.39 | 10 0.39 | M 8 | M 8 | 10 0.39 | 42.5 1.67 | 42.5 1.67 | 22.5 0.89 | 22.5 0.89 | - | - | 5 | 5 | 45 |

Dimensions in: millimeters - inches

Specification

- Housing
Aluminum
Painted, white aluminum **AW**
 - Fastening set
Screws and T-slot nuts
Steel, zinc plated, blue passivated finish **SZ**
 - Slot adapter (for $l_1 = 28$)
Plastic
 - Guide pins (for $l_1 = 40$)
Plastic
- RoHS



Information

Rotating angle brackets GN 41b connect two crossed aluminum profiles at an any angle. Machining of the profile is not necessary.

Depending on the installation situation for the rotating angle bracket, it may be necessary to break off the guide steps or leave out the guide pins.

see also...

- Aluminum Profiles GN 10b (Profile Type Light) → page QVX
- Aluminum Profiles GN 10b (Profile Type Heavy) → page QVX

How to order

GN 41b-40 10 10-C-AWSZ

| | |
|----------|-----------------------------------|
| 1 | Length l_1 |
| 2 | Slot width n_1 |
| 3 | Slot width n_2 |
| 4 | Type |
| 5 | Finish (Housing) |
| 6 | Material / Finish (Fastening set) |