



4 Type

C With fastening set

Metric table

Dimensions in: millimeters - inches

1	2	3									
l_1	n_1	n_2	d_1	d_2	l_2	l_3	m_1	m_2	A/F_1 in mm	A/F_2 in mm	
24 0.94	6 0.24	6 0.24	M 6	M 6	27 1.06	27 1.06	15 0.59	15 0.59	4	4	
32 1.26	8 0.31	8 0.31	M 8	M 8	36 1.41	36 1.41	20 0.79	20 0.79	5	5	

Specification



- Housing
Zinc die-cast
Painted, white aluminum **ZW**
- Fastening set
Screws, T-nuts and bushing
Steel, zinc plated, blue passivated finish **SZ**
- RoHS

Information

Rotating angle brackets GN 41i connect two intersecting aluminum profiles, rotatably mounted via a bushing. Machining of the profile is not necessary.

see also...

- Aluminum Profiles GN 10i (Profile Type Light) → page QVX
- Aluminum Profiles GN 10i (Profile Type Heavy) → page QVX
- Aluminum Profiles GN 11i (with Partially Closed Slots) → page QVX

How to order

GN 41i-32 8 8-C-ZWSZ

1	Length l_1
2	Slot width n_1
3	Slot width n_2
4	Type
5	Finish (Housing)
6	Material / Finish (Fastening set)