



SS Stainless Steel

**Metric table**

d <sub>1</sub>		Length l ±0.25			d <sub>2</sub>	d <sub>3</sub>	h <sub>1</sub>	h <sub>2</sub>	h <sub>3</sub>	h <sub>4</sub>	r	s max.
Stainless Steel	Steel											
6 0.24	-	55* 2.17	64 2.52	88* 3.46	M 6	12 0.47	21 0.83	27.5 1.08	9.5 0.37	10 0.39	6 0.24	4 0.16
10 0.39	10 0.39	100 3.94	120 4.72	180 7.09	M 10 x 1	18 0.71	34 1.34	43 1.69	14 0.55	14 0.55	12 0.47	6 0.24

Dimensions in: millimeters - inches

\* suitable for 19" rack and enclosure layout

**Specification**

- Steel **ST**
- Chrome plated finish **CR**
- Stainless steel AISI 303 **NI**
- Matte shot-blasted finish **GS**
- Hex nuts ISO 8675
- Stainless steel AISI 304
- Location disks DIN 125
- Stainless steel AISI 304
- [Load Rating Information](#) → page 2068
- [Stainless Steel Characteristics](#) → page 2143
- [RoHS compliant](#)

**Information**

GN 425.2 folding handles are used in such applications where minimal protrusion is required. In both positions the handle is retained by a spring loaded detent pin.

**see also...**

- [Folding Cabinet "U" Handles GN 425.8 \(with Locking or Spring-Loaded Return\)](#) → page 163
- [Folding Handles GN 425.9 \(with / without Retaining Spring\)](#) → page 162
- [Folding Handles EN 825.1 \(Plastic, with Spring-Loaded Return\)](#) → [www.jwwinco.com](http://www.jwwinco.com)

How to order (Steel)

**GN 425.2-ST-10-120-CR**

1	Material
2	Handle width d <sub>1</sub>
3	Length l
4	Finish