



Metric table

Dimensions in: millimeters - inches

d ₁	Length l ±0.25		d ₂	h	r	t min.
	Finish SW / SR / BL	Finish SMA / WSA				
20 0.79	200 7.87	200 7.87	M 8	68 2.68	22 0.87	15 0.59
20 0.79	250 9.84	250 9.84	M 8	68 2.68	22 0.87	15 0.59
20 0.79	300 11.81	300 11.81	M 8	68 2.68	22 0.87	15 0.59
20 0.79	350 13.78	-	M 8	68 2.68	22 0.87	15 0.59
28 1.10	250 9.84	250 9.84	M 10	78 3.07	32 1.26	15 0.59
28 1.10	300 11.81	300 11.81	M 10	78 3.07	32 1.26	15 0.59
28 1.10	350 13.78	-	M 10	78 3.07	32 1.26	15 0.59
28 1.10	400 15.75	400 15.75	M 10	78 3.07	32 1.26	15 0.59

Specification

- Aluminum **AL**
 - Powder coated, textured finish
 - Black, RAL 9005
 - Silver, RAL 9006
 - Powder coated, antimicrobial
 - Black, RAL 9005
 - White, RAL 9016
 - Plain, tumbled finish
- SW
 SR
 SMA
 WSA
 BL
- [Load Rating Information](#) → page 2068
 - [RoHS compliant](#)

Accessory

- GN 181 Mounting Plate Sets (Mounting from the Operator’s Side) → page XYZ

On request

- Special designs
- Various metric size fasteners and kit packaging

Information

GN 426 cabinet “U” handles are manufactured from a bent aluminum profile and have excellent stability and ergonomic design.

In addition to the standard finishes, these cabinet “U” handles are also available with a functional coating: The **SMA / WSA** versions have a powder coating based on silver ions, which gives them antimicrobial properties. The principle of action has been shown to reduce the contamination of the handle surfaces within 24 hours so that fewer than 1% of bacteria and fewer than 5% of viruses ultimately survive.

Standard parts with antimicrobial plastic coating are primarily used in the health care sector and in public buildings, such as airports, train stations, stadiums, etc.

see also...

- [Product Family Sanline](#) → page 2131
- [Cabinet “U” Handles GN 428 \(Aluminum\)](#) → page 153

How to order	
1	Material
2	Handle diameter d ₁
3	Length l
4	Finish

1 2 3 4
GN 426-AL-28-300-SW