



Metric table

Dimensions in: millimeters - inches

d ₁	Length l	d ₂	h ₁	h ₂	r	t min.
20 0.79	200 7.87	M 8	105 4.13	68 2.68	22 0.87	15 0.59
20 0.79	300 11.81	M 8	105 4.13	68 2.68	22 0.87	15 0.59
28 1.10	250 9.84	M 10	125 4.92	78 3.07	32 1.26	15 0.59
28 1.10	350 13.78	M 10	125 4.92	78 3.07	32 1.26	15 0.59
28 1.10	500 19.69	M 10	125 4.92	78 3.07	32 1.26	15 0.59

Specification

- Aluminum **AL**
- Powder coated
 - Black, RAL 9005, textured finish **SW**
 - Silver, RAL 9006, textured finish **SR**
 - Plain, tumbled finish **BL**
- Load Rating Information → page 2068
- RoHS compliant

Information

- GN 426.1 cabinet “U” handles are manufactured from a bent aluminum profile.
- see also...
- Cabinet U-Handles GN 565.2 (Aluminum, Mounting from the Back or from the Operator's Side) → page 106
 - Cabinet U-Handles GN 425.1 (Ø 8, 10, 12 mm, Offset Aluminum / Stainless Steel) → page 144
 - Tubular Handles GN 333 (with Angled Legs) → page 168

Accessory

- GN 181 Mounting Plate Sets (Mounting from the Operator's Side) → page XYZ

On request

- Various metric size fasteners and kit packaging

How to order	
1	Material
2	Handle diameter d ₁
3	Length l
4	Finish

1 2 3 4
GN 426.1-AL-28-250-SW