



SS Stainless Steel

3 Type

- A Mounting from the back (tapped blind hole)
- B Mounting from the operator's side

Metric table

Dimensions in: millimeters - inches

1 d ₁	2 l ₁ ±0.5 Type A	±0.3 Type B Tapped hole for mounting stud	d ₂	d ₃	h	l ₂	r ≈	t ₁	t ₂
20 0.79	200 7.87	200 7.87	M 8	-	68 2.68	20 0.79	22 0.87	15 0.59	-
20 0.79	250 9.84	250 9.84	M 8	-	68 2.68	20 0.79	22 0.87	15 0.59	-
20 0.79	300 11.81	300 11.81	M 8	-	68 2.68	20 0.79	22 0.87	15 0.59	-
20 0.79	350 13.78	350 13.78	M 8	-	68 2.68	20 0.79	22 0.87	15 0.59	-
28 1.10	250 9.84	250 9.84	M 10	32 1.26	90 3.54	20 0.79	32 1.26	-	17 0.67
28 1.10	300 11.81	300 11.81	M 10	32 1.26	90 3.54	20 0.79	32 1.26	-	17 0.67
28 1.10	350 13.78	350 13.78	M 10	32 1.26	90 3.54	20 0.79	32 1.26	-	17 0.67
28 1.10	400 15.75	400 15.75	M 10	32 1.26	90 3.54	20 0.79	32 1.26	-	17 0.67

Specification

- Stainless steel AISI 304
Matte shot-blasted finish
d₁ = 20 mm: solid material
d₁ = 28 mm: tube Ø 28x2 mm
- Tapped insert / mounting stud
Stainless steel AISI 303
- Set screw (Type B)
d₁ = 20 mm: DIN 914-M5-6-NI
d₁ = 28 mm: DIN 914-M6-8-NI
- Load Rating Information → page 2068
- Stainless Steel Characteristics → page 2143
- RoHS compliant

On request

- Various metric size fasteners and kit packaging

Information

GN 426.5 cabinet U-handles can be mounted from the back (type A) as well as from the operator's side (type B). In this case the stud is first screwed in from the machine side and then the handle is pushed on and secured with the set screw.

Both mounting methods allow the mounting of a pair of handles in opposite position. This method could be used e.g. on doors (double handle). In general, a mounting stud with special length l₂ might be required.

see also...

- Cabinet U-Handles GN 426 (Aluminum) → page 146
- Tubular Grip Handles GN 666.5 / GN 666.7 (Stainless Steel) → page 186

<p>How to order</p> <p>GN 426.5-28-400-A</p>	1	Handle diameter d ₁
	2	Length l ₁
	3	Type

1.1
1.2
1.3
1.4
2.1
2.2
2.3
2.4