



SS Stainless Steel

Metric table

Dimensions in: millimeters - inches

b	Length l ±0.25	a	h	r
12 0.47	55* 2.17	8 0.31	40 1.57	8 0.31
12 0.47	88* 3.46	8 0.31	40 1.57	8 0.31
12 0.47	100 3.94	8 0.31	40 1.57	8 0.31
12 0.47	120* 4.72	8 0.31	40 1.57	8 0.31
12 0.47	180* 7.09	8 0.31	40 1.57	8 0.31
12 0.47	200 7.87	8 0.31	40 1.57	8 0.31
12 0.47	235* 9.25	8 0.31	40 1.57	8 0.31

* Suitable for 19" rack and enclosure layout

Specification

- **GN 427**
Aluminum
 - Powder coated
 - Black, RAL 9005, textured finish ● **SW**
 - Silver, RAL 9006, textured finish ● **SR**
 - Anodized finish, natural color ● **EL**
- **GN 427.5**
Stainless steel AISI 304
Matte shot-blasted finish
- [Load Rating Information](#) → page 2068
- [Stainless Steel Characteristics](#) → page 2143
- [RoHS compliant](#)

On request

- Special lengths
- Various metric size fasteners and kit packaging

Information

GN 427 and GN 427.5 cabinet "U" handles are manufactured from a bent aluminum / stainless steel profile.

The manufacturing process allows the production of special lengths in relatively small quantities.

see also...

- [Cabinet "U" Handles GN 425 \(Aluminum / Stainless Steel\)](#) → page 138

How to order (Aluminum)	1 Handle diameter b
↓ ↓ ↓	2 Length l
GN 427-12-120-EL	3 Finish

How to order (Stainless steel)	1 Handle diameter b
↓ ↓	2 Length l
GN 427.5-12-180	

1.1
1.2
1.3
1.4
2.1
2.2
2.3
2.4