



**Metric**

iF product design award  
 GERMAN DESIGN AWARD  
 reddot design award winner

**4 Type**

**A** Mounting from the back (tapped blind hole)

**B** Mounting from the operator's side

**Metric table**

Dimensions in: millimeters / inches

<b>b</b>	<b>l<sub>1</sub></b>	<b>a</b>	<b>d</b>	<b>h<sub>1</sub></b>	<b>h<sub>2</sub></b>	<b>l<sub>2</sub></b>	<b>l<sub>3</sub></b>	<b>l<sub>4</sub></b>	<b>t</b>
28 1.10	200 7.87	18 0.71	M 8	63 2.48	11.8 0.46	240 9.45	30 1.18	10 0.39	10 0.39
28 1.10	250 9.84	18 0.71	M 8	63 2.48	11.8 0.46	290 11.42	30 1.18	10 0.39	10 0.39
28 1.10	300 11.81	18 0.71	M 8	63 2.48	11.8 0.46	340 13.39	30 1.18	10 0.39	10 0.39
28 1.10	400 15.75	18 0.71	M 8	63 2.48	11.8 0.46	440 17.32	30 1.18	10 0.39	10 0.39
36 1.42	300 11.81	26 1.02	M 10	71 2.80	16.6 0.65	355 13.98	40 1.57	13 0.51	14 0.55
36 1.42	400 15.75	26 1.02	M 10	71 2.80	16.6 0.65	455 17.91	40 1.57	13 0.51	14 0.55
36 1.42	500 19.69	26 1.02	M 10	71 2.80	16.6 0.65	555 21.85	40 1.57	13 0.51	14 0.55
36 1.42	600 23.62	26 1.02	M 10	71 2.80	16.6 0.65	655 25.79	40 1.57	13 0.51	14 0.55
36 1.42	800 31.50	26 1.02	M 10	71 2.80	16.6 0.65	855 33.66	40 1.57	13 0.51	14 0.55

**Specification**

**Handle**

Aluminum

**AL**

• Powder coated

- Black, RAL 9005, textured finish

- Silver, RAL 9006, textured finish

• Anodized finish, natural color

● **SW**

● **SR**

● **EL**

**Fastening set (Type B)**

Stainless steel AISI 304

• Socket button head screws ISO 7380

• Hex nuts ISO 4032

• Washers DIN 125

RoHS

**On request**

• Other finishes or special designs

• Various metric size fasteners along with kit packaging

Cabinet U-handles GN 428 are manufactured from a bent aluminum profile and have excellent stability and ergonomic design.

For type B, socket button head screws, hex nuts and washers are included. Especially in combination with the smaller cabinet U-handles GN 328, they meet the requirements of modern industrial design.

see also...

**GN 328** Cabinet U-Handles

**GN 426** Cabinet U-Handles

Page

QVX

QVX

**Technical Information**

Load Capacity Information

Stainless Steel Characteristics

QVX

QVX

**How to order**

<b>1</b>	<b>Material</b>
<b>2</b>	<b>Handle diameter b</b>
<b>3</b>	<b>Length l<sub>1</sub></b>
<b>4</b>	<b>Type</b>
<b>5</b>	<b>Finish</b>

**GN 428-AL-28-300-A-SW**

1.1  
1.2  
1.3  
1.4  
2.1  
2.2  
2.3  
2.4

