



**SS** Stainless Steel

**Metric table**

Dimensions in: millimeters - inches

<sup>2</sup> d <sub>1</sub>	<sup>3</sup> Length l ±0.5			<sup>4</sup> h		d <sub>2</sub>	r	t min.
12 0.47	125 4.92	160 6.30	200 7.87	75 2.95	110 4.33	M 6	14 0.55	12 0.47
16 0.63	160 6.30	200 7.87	300 11.81	85 3.35	125 4.92	M 6	18 0.71	12 0.47

**Specification**

- Stainless steel AISI 303 **NI**
- Matte shot-blasted finish **GS**
- Powder coated Black, RAL 9005, textured finish **● SW**
- *Load Rating Information* → page 2068
- *Stainless Steel Characteristics* → page 2143
- *RoHS compliant*

**On request**

- Other dimensions
- Other materials
- Other finishes

**Information**

GN 435 cabinet U-handles in tall design are made from bent round profiles and are designed for applications requiring a greater height for gripping. For example, this makes it possible to grab or hold the handle while wearing safety gloves. Some dimensions also comply with the crane access standard DIN EN 13856.

In addition to serving as a handle, they can also be used as hose guides, retaining brackets or similar.

see also...

- *Cabinet U-Handles GN 425 (Stainless Steel)* → page 138
- *Cabinet U-Handles GN 435.3 (Stainless Steel, Weldable)* → page 143
- *Cabinet U-Handles GN 426.5 (Stainless Steel)* → page 147
- *Tubular Cabinet U-Handles GN 426.3 (Steel, Weldable)* → page 149
- *Cabinet U-Handles GN 565.5 (Stainless Steel)* → page 100

How to order	
<sup>1</sup>	Material
<sup>2</sup>	Handle diameter d <sub>1</sub>
<sup>3</sup>	Length l
<sup>4</sup>	Height h
<sup>5</sup>	Finish

<sup>1</sup> <sup>2</sup> <sup>3</sup> <sup>4</sup> <sup>5</sup>  
**GN 435-NI-12-160-75-SW**

1.1  
1.2  
1.3  
1.4  
2.1  
2.2  
2.3  
2.4