



Marking opposite socket set screw



SS Stainless Steel

3 Type

- N Without indicator point
- M With indicator point

Metric table

Dimensions in: millimeters - inches

1 d ₁	2 d ₂ H8 Bore		d ₃	h	Length l	t min.
24 <i>0.94</i>	B 5	B 6	M 4	16 <i>0.63</i>	4 <i>0.16</i>	10 <i>0.39</i>
28 <i>1.10</i>	B 6	B 8	M 4	18 <i>0.71</i>	4 <i>0.16</i>	11 <i>0.43</i>

Specification

- Stainless steel AISI 304
Matte shot-blasted finish **MT**
- Indicator point (Type M)
Laser engraved
- Socket set screw DIN 916
Stainless steel
with internal hex and serrated point
- [Stainless Steel Characteristics](#) → page QVX
- [RoHS compliant](#)

Information

- see also...
- [Knurled Nuts GN 536 \(Stainless Steel\)](#) → page QVX

How to order

GN 436-24-B6-N-MT

- 1** Outside diameter d₁
- 2** Bore d₂
- 3** Type
- 4** Finish

