



Metric



**3 Type**

L L-shaped

**4 Identification no.**

- 1 Short
- 2 Long

**Metric table**

**2**

Dimensions in: millimeters / inches

| l <sub>1</sub> | d           | l <sub>2</sub> |              | l <sub>3</sub> | m <sub>1</sub> | m <sub>2</sub> |            | m <sub>3</sub> |              | m <sub>4</sub> | m <sub>5</sub> | s         | For aluminum profiles with grid size |           |
|----------------|-------------|----------------|--------------|----------------|----------------|----------------|------------|----------------|--------------|----------------|----------------|-----------|--------------------------------------|-----------|
|                |             | ld. no. 1      | ld. no. 2    |                |                | ld. no. 1      | ld. no. 2  | ld. no. 1      | ld. no. 2    |                |                |           | ld. no. 1                            | ld. no. 2 |
| 50<br>1.97     | 4.2<br>0.17 | 22<br>0.87     | 33.5<br>1.32 | 18.5<br>0.73   | 40<br>1.57     | 9.5<br>0.37    | 11<br>0.43 | 7<br>0.28      | 15.5<br>0.61 | 8.9<br>0.35    | 5<br>0.20      | 2<br>0.08 | 20                                   | 30        |
| 68<br>2.68     | 4.2<br>0.17 | 32<br>1.26     | 51<br>2.01   | 21.5<br>0.85   | 55<br>2.17     | 11<br>0.43     | 11<br>0.43 | 14<br>0.55     | 33<br>1.30   | 9.5<br>0.37    | 7<br>0.28      | 2<br>0.08 | 30                                   | 40 / 45   |
| 80<br>3.15     | 5.2<br>0.20 | -              | 49<br>1.93   | 24.5<br>0.96   | 65<br>2.56     | -              | 11<br>0.43 | -              | 31<br>1.22   | 11.5<br>0.45   | 7<br>0.28      | 2<br>0.08 | -                                    | 40 / 45   |

**Specification**

**1**

**5**

Stainless steel AISI 316

**A4**

Matte shot-blasted finish

**GS**

RoHS

Mounting plates GN 4490.1 enable the use of ball catches GN 4490 in various installation situations. The positioning is facilitated by slotted holes.

see also...

**GN 4490** Ball Catches

**Page**

QVX

**GN 4490.2** Mounting Plates (for Mounting Blocks)

QVX

**Technical Information**

Stainless Steel Characteristics

QVX

**Accessory**

**GN 50b** T-Nuts

QVX

**GN 50i** T-Nuts

QVX

**GN 51b** T-Slot Nuts

QVX

**How to order**

|          |                       |
|----------|-----------------------|
| <b>1</b> | Material              |
| <b>2</b> | Length l <sub>1</sub> |
| <b>3</b> | Type                  |
| <b>4</b> | Identification no.    |
| <b>5</b> | Finish                |

**GN 4490.1-A4-68-L-1-GS**

3.1  
3.2  
3.3  
3.4  
3.5  
3.6  
3.7  
3.8  
3.9  
3.10

